

Aluminized Preox® Herringbone With Chloroprene Coating	
Style Number	1100-3
Description	Preox Herringbone
Coating Face	Gentex® Dual Mirror® Aluminized Fabric
Coating Back	Chloroprene
Certifications	EN 407

Characteristics

	Test Method	English	Metric
Areal Weight	ASTM D3776	17.0 oz / sq yd	575 gms / sq m
Thickness			
Breaking Strength	ASTM D5034		
Trapezoidal Tear			
Warp		240.0 lb	1066.0 N
Fill		160.0 lb	710.0 N
Tear Strength	ASTM D1424		
Elmendorf Tear			
Warp		6.0 lbs	27.0 N
Fill		8.0 lbs	36.0 N
Flame Resistance	ASTM D6413		
After Flame		2.0 sec	2.0 sec
Char Length		1.0 in	2.5 cm
Radiant Reflectivity	MIL-C-24929A	25.0 sec	25.0 sec

Style Number: 1100-3

Comprehensive Fabric Line

Field proven for over 50 years, Gentex delivers the most durable aluminized fabrics in the industry. Each roll of Gentex Dual Mirror Aluminized Fabric is thoroughly tested and provides uncompromising function, appearance, and superior performance even in the most demanding applications. With over twenty aluminized fabrics to choose from and an expert team to guide you in your selection, you can be assured you'll get the right fabric for your specific needs. To view and learn more about our full line of fabrics visit, www.gentexcorp.com/aluminizedfabric.

GENTEX®

**DUAL
MIRROR®**